



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S49396 100W Led Hid Replcmnt 50K Mog Ext Base 14300LM

Satco

Catalog Number	S49396
Manufacturer	Satco
Description	100 Watt Led Hid Replacement - 5000K - Extended Mogul Base - Type B Ballast Bypass - Economy Hi-Pro
Weight per unit	3.8 (lbs/each)
Product Category	Lighting

Features

average life	35000
Base	Extended Mogul
beam angle	300
Shape	Corncob

Material, Color, and Finish

Finish	white
--------	-------

Dimensions and Weight

Size	9.67
------	------

Descriptions

Description	100W LED HID REPLCMNT 50K MOG EXT BASE 14300LM
extra long description	SATCO S49396 100W/LED/HP/850/100-27
Long Description	100 Watt LED HID Replacement - 5000K - Extended Mogul Base - Type B Ballast Bypass - Economy Hi-Pro
Product Type	100W/Led/HP/850/100-277V/Ex39
Special Features	Lawful for sale in California ; Lumens: 13800 ; CCT: 5000K ; Color Temperature: Natural Light ; Dimmable: Non-Dimmable ; Lamp Appearance: Clear ; MOL: 9.67 in. ; MOD: 4.72 in. ; Weight: 3.53 lb. ; Warranty: 3 Year Limited ; Brand: Hi-Pro ; Enclosure Rating: Enclosed Rated Lamp ; FCC Compliant: Yes ; Ballasting Requirements: Ballast Bypass ; HID Equivalent: 400W ; Indoor/Outdoor: Indoor and Outdoor ; IP Rating: IP65 ; Lamp Ballast: Type B ; Mounting: Base Up or Base Down Only ; Operating Temperature: -30C (

Manufacturer Information

Brand	Satco
GTIN	00045923493966
Manufacturers Part Number	S49396
UPC	045923493966



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Type Corncob

Packaging

Carton 1

Weight Per each 3.802

Uses, Certifications, and Standards

standard cULus Classified - cULus Listed