



S7228

23T2/41
23 watt; Mini Spiral Compact Fluorescent; 4100K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7228

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|-------------------------------|---------------|----------------|-------------------------|--------------------------------|------------|-----------|
| S7228 | 045923072284 | 120 | 23 | 100W | T2 | Medium | E26 |
| Lamp Code | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 23T2/41 | 4.88" | 2.13" | 1600 | 12000 | 4100 | Cool White | 48/12 |
| CRI | CEC Status | Hg Content | RoHS Compliant | UL or ETL Listed | Warranty | | |
| 82 | Lawful for sale in California | 1.6 mg | Yes | Yes | 2 Year Limited | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7228

23T2/41
23 watt; Mini Spiral Compact Fluorescent; 4100K; 82 CRI;
Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7228

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S7228 | 045923072284 | 120 | 23 | 100W | T2 | Medium | E26 |

| Lamp Code | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
|-----------|---------------|---------------|----------------|---------------------|-------------|------------|-------|
| 23T2/41 | 4.88" | 2.13" | 1600 | 12000 | 4100 | Cool White | 48/12 |

| CRI | CEC Status | Hg Content | RoHS Compliant | UL or ETL Listed | Warranty |
|-----|-------------------------------|------------|----------------|------------------|--------------------------------|
| 82 | Lawful for sale in California | 1.6 mg | Yes | Yes | 2 Year Limited |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

