



S7304

15G25/27
15 watt; G25 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7304

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Incandescent Equivalent |
|--------------|---------------|---------------|----------------|---------------------|-------------|------------|-------------------------|
| S7304 | 045923073045 | 15 | G25 | Medium | E26 | 15G25/27 | 60W |
| Voltage | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 120 | 4.72" | 3.44" | 820 | 10000 | 2700 | Warm White | 48/12 |
| Package Type | CRI | ENERGY STAR | RoHS Compliant | UL Listed | | | |
| Box | 82 | ENERGY STAR | Yes | Yes | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S7304

15G25/27
15 watt; G25 Compact Fluorescent; 2700K; 82 CRI; Medium base; 120 volts

Features

- Self-ballasted Spiral CFL
- Uses 75% less energy than equivalent incandescent lamps
- Long Life
- Instant On



S7304

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Incandescent Equivalent |
|--------------|---------------|---------------|----------------|---------------------|-------------|------------|-------------------------|
| S7304 | 045923073045 | 15 | G25 | Medium | E26 | 15G25/27 | 60W |
| Voltage | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 120 | 4.72" | 3.44" | 820 | 10000 | 2700 | Warm White | 48/12 |
| Package Type | CRI | ENERGY STAR | RoHS Compliant | UL Listed | | | |
| Box | 82 | ENERGY STAR | Yes | Yes | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

