



S9134

10BR30/LED/3000K/800L/120V/D
10 watt; BR30 LED; 108' beam spread; 3000K; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

Top 3 Recommended Dimmers

- Lutron® CT-600P
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S9134

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------------------|---------------|---------------|----------------|---------------------|----------------|------------------------------|---------|
| S9134 | 045923091346 | 10 | BR30 | Medium | E26 | 10BR30/LED/3000K/800L/120V/D | 120 |
| Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | CRI |
| Frosted | 5 3/16" | 3.75" | 800 | 25000 | 3000 | Warm White | 80 |
| Incandescent Equivalent | Pack | Package Type | Beam Spread | ENERGY STAR | RoHS Compliant | UL or ETL Listed | |
| 65W | 12/6 | Box | 108 | ENERGY STAR | Yes | Yes | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9134

10BR30/LED/3000K/800L/120V/D
10 watt; BR30 LED; 108' beam spread; 3000K; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

Top 3 Recommended Dimmers

- Lutron® CT-600P
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S9134

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | Voltage |
|-------------------------|---------------|---------------|----------------|---------------------|----------------|------------------------------|---------|
| S9134 | 045923091346 | 10 | BR30 | Medium | E26 | 10BR30/LED/3000K/800L/120V/D | 120 |
| Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp | Color | CRI |
| Frosted | 5 3/16" | 3.75" | 800 | 25000 | 3000 | Warm White | 80 |
| Incandescent Equivalent | Pack | Package Type | Beam Spread | ENERGY STAR | RoHS Compliant | UL or ETL Listed | |
| 65W | 12/6 | Box | 108 | ENERGY STAR | Yes | Yes | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

