



# S9639

16.5BR40/LED/3000K/1230L/120V  
16.5 watt; LED BR40; 3000K; 103' beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9639

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9639	DiTTO	045923096396	120	16.5	75W	0.92	BR40

  

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	16.5BR40/LED/3000K/1230L/120V	Dimmable	Frosted	6 7/16"	5.00"	1230

  

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant
25000	3000	Warm White	80	103	12/6	Box	Yes

  

UL or ETL Listed	UL Classification	Warranty
Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9639

16.5BR40/LED/3000K/1230L/120V  
16.5 watt; LED BR40; 3000K; 103' beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9639

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9639	DiTTO	045923096396	120	16.5	75W	0.92	BR40
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	16.5BR40/LED/3000K/1230L/120V	Dimmable	Frosted	6 7/16"	5.00"	1230
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant
25000	3000	Warm White	80	103	12/6	Box	Yes
UL or ETL Listed	UL Classification		Warranty				
Yes	cULus - Damp Location Rated		<a href="#">3 Year Limited</a>				



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

