

Eaton S811 V36N3S

Catalog Number: S811+V36N3S

Eaton S811+ soft starter, Non-combination Soft Starter, Frame size 290 mm, 360 A, 600 V, Three-pole

General specifications



Photo is representative

Product Name

Eaton S811+ soft starter

Catalog Number

S811+V36N3S

UPC

786685559094

Product Length/Depth

16.57 in

Product Height

7.35 in

Product Width

11.05 in

Product Weight

48 lb

Compliances

CE Marked

Certifications

IEC 60947-4-2

EN 60947-4-2

UL Listed

CSA Certified

defaultTaxonomyAttributeLabel

Amperage Rating

360A

Number Of Poles

Three-pole

Type

Soft starter

Voltage rating

600 V

Frame size

290 mm

Resources

Application notes

S8xL adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - S811+V36N3S

Drawings

Type S811+ Soft Starter - V-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V

Multimedia

Soft Starter Product Family Overview

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

Specifications and datasheets

Eaton Specification Sheet - S811+V36N3S



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton S811 V36N3S

Catalog Number: S811+V36N3S

Eaton S811+ soft starter, Non-combination Soft Starter, Frame size 290 mm, 360 A, 600 V, Three-pole

General specifications



Photo is representative

Product Name
Eaton S811+ soft starter

Catalog Number
S811+V36N3S

UPC
786685559094

Product Length/Depth
16.57 in

Product Height
7.35 in

Product Width
11.05 in

Product Weight
48 lb

Compliances
CE Marked

Certifications
IEC 60947-4-2
EN 60947-4-2
UL Listed
CSA Certified

Amperage Rating

360A

Number Of Poles

Three-pole

Type

Soft starter

Voltage rating

600 V

Frame size

290 mm

Application notes

[S8xL adjustment - Switching from S801+ to S811+](#)

Brochures

[S811+/S801+ soft starters](#)

Catalogs

[Product Range Catalog Drives Engineering](#)[Eaton's Volume 6—Solid-State Motor Control](#)[Product Datasheet - S811+V36N3S](#)

Drawings

[Type S811+ Soft Starter - V-frame](#)

Installation instructions

[Instructions for S811+ Soft Starter, S811+T..., S811+U..., and S811+V](#)

Multimedia

[Soft Starter Product Family Overview](#)[Soft starter DS7 up to 200 A](#)[Soft Starter DS7 up to 32 A](#)

Specifications and datasheets

[Eaton Specification Sheet - S811+V36N3S](#)

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)