



S8129

F21T5/835/ENV
21 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;
Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8129

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8129 | 045923081293 | 21 | T5 | Miniature Bi Pin | G5 | F21T5/835/ENV | 0.63" |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 34" | 36" | 2100 | 1950 | 24000 | 3500 | Neutral White | 40 |
| Package Type | CRI | RoHS Compliant | | | | | |
| Sleeve | 85 | Yes | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S8129

F21T5/835/ENV
21 watt; T5; Fluorescent; 3500K Neutral White; 85 CRI;
Miniature Bi Pin base

Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8129

| Item Number | UPC | Watts | Lamp Shape | Base | ANSI Base | Lamp Code | MOD In Inches |
|---------------|----------------|----------------|-------------|---------------------|-------------|---------------|---------------|
| S8129 | 045923081293 | 21 | T5 | Miniature Bi Pin | G5 | F21T5/835/ENV | 0.63" |
| MOL In Inches | Nominal Length | Initial Lumens | Mean Lumens | Average Rated Hours | Kelvin Temp | Color | Pack |
| 34" | 36" | 2100 | 1950 | 24000 | 3500 | Neutral White | 40 |
| Package Type | CRI | RoHS Compliant | | | | | |
| Sleeve | 85 | Yes | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

