



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SB1810S Easy Twist Crimp Sleeve S

Nsi Industries

Catalog Number	SB1810S
Manufacturer	Nsi Industries
Description	The Easy-Twist SB1810S 100-Count Pack Of Steel Crimp Sleeve Wire Connectors Are Designed For Use On Wires In The 18-10 Awg Size Range. The Simple Brass-Plated Sleeve Design Forms Low-Resistance Connections In A Tight Space and Installs Using A Specialized Crimp Tool or Adjustable Pliers. Use Crimp Sleeves to Permanently Connect Wires In Grounding, Uninsulated or Small Motor Applications Where Vibration Resistance Is A Concern.
Weight per unit	0.2300 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Steel
Number of Conductors	1
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	18-10 AWG
Wire Type	CU Wire Only

Material, Color, and Finish

Color	Steel
Finish	Steel

Dimensions and Weight

Size	L=.374 - W=.240 - ID=.204
------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	EASY TWIST CRIMP SLEEVE S
extra long description	NSI SB1810S Easy Twist Crimp Sleeve
Features	Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. The steel crimp sleeve wire connector provides a quick, economic and vibration-resistant way to form permanent connections in most applications. Simply twist your wires to form a connection, then slide the sleeve "sometimes called a ground cap" down to the twist and crunch it tight with adjustable pliers or a specialized crimping tool. We designed these brass-plated steel cri
Long Description	The Easy-Twist SB1810S 100-Count Pack of Steel Crimp Sleeve Wire Connectors are designed for use on wires in the 18-10 AWG size range. The simple brass-plated sleeve design forms low-resistance connections in a tight space and installs using a specialized crimp tool or adjustable pliers. Use crimp sleeves to permanently connect wires in grounding, uninsulated or small motor applications where vibration resistance is a concern.
Product Type	Easy Twist Crimp Sleeve Steel 18-10
Special Features	Steel Crimp Sleeves - 100 Pcs Blister

Manufacturer Information

Brand	NSi
GTIN	00662381402448
Manufacturers Part Number	SB1810S
UPC	662381402448

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Crimp Sleeve Wire Connectors

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Splicing Wire
environmental conditions	105 C
standard	UL 486C
Temperature Rating	105 C