



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SDL615940D 6" 15.5W Led Disk 40K

Topaz - Southwire LLC

Catalog Number	SDL615940D
Manufacturer	Topaz - Southwire LLC
Description	Disk Light, Bathrooms;Closets;Commercial;Hallways and Living Areas;Residential;Storage Areas Application, 50000 H Average Life, 1050 LM Brightness (Lumens), Incandescent Bulb Type, Energy Star, Made In Usa, +104 °F Maximum Operating Temperature, -4 °F Minimum Operating Temperature, 1 Ca;24 PK Package Quantity, Advanced Optics and Thermal Construction;Surface Mount to Most 4" J-Boxes;Up to 85% Energy Savings Compared to Incandescent Lamps Special Features, Compliant With Nfpa 70;Nec Section 410.16 (A)(3) An
Weight per unit	0.9000 (lbs/each)
Product Category	Lighting

### Descriptions

Description	6" 15.5W LED DISK 40K
extra long description	WHITE FINISH; 7.4 INCH; 1 LAMP(S); 15 WATT WATTAGE; YES LAMP INCLUDED; LED, DIMMABLE LAMP TYPE; ROHS COMPLIANT; SIZE 6 INCH; INPUT VOLTAGE RATING 120 VOLT; INTENSITY 1090 LUMEN; COLOR TEMPERATURE 4000 KELVIN; COLOR RENDERING INDEX 90; TEMPERATURE RATING -4 TO 104 DEG F; RATED LIFE 50000 HOUR; EQUIVALENT 100 WATT; MOUNTING TYPE SURFACE; APPLICATION RESIDENTIAL, COMMERCIAL, BATHROOM, CLOSET, STORAGE AREA, HALLWAY AND LIVING AREA, DAMP/WET; APPROVAL UL; APPLICABLE STANDARD NEC 410.16 (A)(3)/(C)(5), TITLE 24,

### Manufacturer Information

Brand	TOPAZ
GTIN	00751338002760
Manufacturers Part Number	SDL6/15/940/D-28
UPC	751338002760

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--------------------------------------------

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	0.9