



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC40 4/0 Cubutt Splice

Nsi Industries

Catalog Number	SC40
Manufacturer	Nsi Industries
Description	Standard Barrel Tinned Copper Splice 4/0 Awg: Standard Barrel Tinned Copper Splices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated To Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.0800 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Purple
Finish	Tin Plated

Dimensions and Weight

Size	L=1.90 - OD=.690 - ID=.550
------	----------------------------

Descriptions

Description	4/0 CUBUTT SPLICE
extra long description	NSI SC-4/0 CU CMP Splice Short 4 AW
Features	Standard Barrel Tinned Copper Splice 4/0 AWG: Standard Barrel Tinned Copper Splices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	Standard Barrel Tinned Copper Splice 4/0 AWG: Standard Barrel Tinned Copper Splices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Splice Short 4 Awg
Special Features	4/0 AWG (STR) - CU Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	NSi
GTIN	00662381037091
Manufacturers Part Number	SC-4/0
UPC	662381037091

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - CU Splice

Packaging

Carton	1
Package	25
Weight Per each	0.08

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A
Temperature Rating	90 C