



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SC8 #8 Cu Butt Splice *Nsi Industries*

Catalog Number	SC8
Manufacturer	Nsi Industries
Description	Standardbarrel TINNEDCOPPERSPLICE8 Awg Standard Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.0140 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	600 V
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Red
Finish	Tin Plated

### Dimensions and Weight

Size	L=.900 - OD=.270 - ID=.170
------	----------------------------

### Descriptions

Description	#8 CU BUTT SPLICE
extra long description	NSI SC-8 CU CMP Splice Short 750 MC
Features	Standard Barrel Tinned Copper Splice for 8 AWG: Standard Barrel Tinned Copper Splices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	StandardBarrel TinnedCopperSplice8 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Splice Short 750 MCM
Special Features	# 8 AWG (STR) - CU Splice



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381037008
Manufacturers Part Number	SC-8
UPC	662381037008

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - CU Splice

## Packaging

Carton	1
Package	100
Weight Per each	0.014

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)
Temperature Rating	90 C