



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SF10PIV Skylark 8A Dimmer Fluorescent SP Ivory

Lutron

Catalog Number	SF10PIV
Manufacturer	Lutron
Description	Skylark Dimmer With On/Off Switch, Fluorescent or Led Dimming With 3-Wire Ballasts and Drivers, Single-Pole, Preset, 120V/8A In Ivory
Weight per unit	0.1000 (lbs/each)
Product Category	Lighting Dimmers

### Features

actuator	Rocker/Slide
amperage rating	8.0000000000000000
connection	Wire Leads
Connection Type	Wire Leads
insulation	Plastic
Material	Plastic/Metal
Poles	1
Switch Type	Slide
Voltage Rating	120
Wattage	960.0000000000000000

### Material, Color, and Finish

Color	Ivory
-------	-------

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	SKYLARK 8A DIMMER FLUORESCENT SP IVORY
extra long description	LUT SF-10P-IV SKYLARK FLUOR 120V 1-
Long Description	Skylark Dimmer with On/Off Switch, Fluorescent or LED Dimming with 3-Wire Ballasts and Drivers, single-pole, preset, 120V/8A in ivory
Product Type	Skylark Fluor 120V 1-10LP Iv
Special Features	Controls 8 A 3-wire LED driver or fluorescent ballast loads. Rocker switch returns light to light level indicated by slider. Slide up to brighten, down to dim.

### Manufacturer Information

Brand	Lutron
GTIN	00027557310253
Manufacturers Part Number	SF-10P-IV
UPC	027557310253



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer with on/off switch, 3-way

## Packaging

Carton	1
Weight Per each	0.1

## Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
Frequency Rating	50 to 60
Mounting	WALLBOX
standard	UL, CSA