



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SG3A0030KB D16 SNTL-G 3PH 30KVA 480D-208Y/120V AI 60HZ 150C 3 *Hammond Power Solutions*

| | |
|------------------|--|
| Catalog Number | SG3A0030KB |
| Manufacturer | Hammond Power Solutions |
| Description | 600V Class Three Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 30 Kva, 3PH, Aluminum Wound |
| Weight per unit | 310.0 (lbs/each) |
| Product Category | Three Phase Energy Efficient D |

Features

| | |
|-------------------|-----------------|
| kva rating | 30 |
| Number of Phases | 3 |
| Number of Taps | ST-20 compliant |
| Phase | 3PH Delta-Wye-N |
| Primary Voltage | 480D |
| Secondary Voltage | 208Y/120 |

Dimensions and Weight

| | |
|--------|------|
| Height | 28.8 |
| Length | 23.8 |
| Width | 25.8 |

Descriptions

| | |
|------------------------|--|
| Description | D16 SNTL-G 3PH 30KVA 480D-208Y/120V AL 60HZ 150C 3 |
| extra long description | HMND SG3A0030KB D16 SNTL-G 3PH 30KV |
| Features | Optional infrared windows available |
| Long Description | 600V Class Three Phase DOE2016 and NRCAN 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 30 kVA, 3PH, Aluminum Wound |
| Product Type | D16 SNTL-G 3PH 30KVA 480D-208Y/120V AI 60HZ 150C 3R |
| Special Features | Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | HPS |
| GTIN | 00803423121952 |
| Manufacturers Part Number | SG3A0030KB |
| UPC | 803423121952 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | 3 PHASE TRANSFORMERS |
| Type | Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Three Phase |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 310 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems. |
| Enclosure | DH2-N3R - Indoor or Outdoor |
| Frequency Rating | 60 |
| Mounting standard | Floor or Wall/Ceiling Mount CSA, UL |
| Temperature Rating | Typical 30 Average/ 40 Maximum |