



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SGABM20AC 3/4X3/4" WHT Super Grip CBL Tie MNT

Panduit Corporation

Catalog Number	SGABM20AC
Manufacturer	Panduit Corporation
Description	The Panduit SGABM20-A-C Super Grip Rubber Adhesive Backed Cable Tie Mounts Are Made Of Nylon 6.6 and Are For Use With Miniature and Intermediate Super-Grip Cross-Section Cable Ties. Designed For Indoor Use, Especially In Areas Where Space Is Limited. They Measure 0.75" X 0.75" (19.1MM X 19.1MM), Supplied In Strips Of 2, Are White In Color and Come In Packages Of 100.
Weight per unit	0.0020 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Polyamide PA
Material	Nylon 6.6
media	Yes

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	3/4X3/4" WHT SUPER GRIP CBL TIE MNT
extra long description	PAN SGABM20-A-C Super-Grip® SGABM20
Long Description	The Panduit SGABM20-A-C super grip rubber adhesive backed cable tie mounts are made of Nylon 6.6 and are for use with miniature and intermediate Super-Grip cross-section cable ties. Designed for indoor use, especially in areas where space is limited. They measure 0.75" x 0.75" (19.1mm x 19.1mm), supplied in strips of 2, are white in color and come in packages of 100.
Product Type	Super-Grip® SGABM20-A-C Super-Grip™ Mount, White, Pa 6.6, Ru

Manufacturer Information

Brand	PANDUIT
GTIN	00074983713561
Manufacturers Part Number	SGABM20-A-C
UPC	074983713561



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie Mount

Packaging

Carton	100
Package	500
Weight Per each	0.002

Uses, Certifications, and Standards

Application	Indoor;Right Angle Mounts Holds Cable Bundles Away from the Sharp Edges of Bulkheads or Cabinet Holes. Can Also be used to Mount Cable Bundles Adjacent to Any Surface
Mounting	Adhesive Tape
Operating Temperature standard	120 CE Compliant,RoHS Compliant