



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SGABM20AC 3/4X3/4" WHT Super Grip CBL Tie MNT *Panduit Corporation*

Catalog Number	SGABM20AC
Manufacturer	Panduit Corporation
Description	The Panduit SGABM20-A-C Super Grip Rubber Adhesive Backed Cable Tie Mounts Are Made Of Nylon 6.6 and Are For Use With Miniature and Intermediate Super-Grip Cross-Section Cable Ties. Designed For Indoor Use, Especially In Areas Where Space Is Limited. They Measure 0.75" X 0.75" (19.1MM X 19.1MM), Supplied In Strips Of 2, Are White In Color and Come In Packages Of 100.
Weight per unit	0.0020 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Polyamide PA
media	Yes

### Material, Color, and Finish

Color	White
-------	-------

### Descriptions

Description	3/4X3/4" WHT SUPER GRIP CBL TIE MNT
extra long description	PAN SGABM20-A-C Super-Grip® SGABM20
Long Description	The Panduit SGABM20-A-C super grip rubber adhesive backed cable tie mounts are made of Nylon 6.6 and are for use with miniature and intermediate Super-Grip cross-section cable ties. Designed for indoor use, especially in areas where space is limited. They measure 0.75" x 0.75" (19.1mm x 19.1mm), supplied in strips of 2, are white in color and come in packages of 100.
Product Type	Super-Grip® SGABM20-A-C Super-Grip™ Mount, White, Pa 6.6, Ru

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983713561
Manufacturers Part Number	SGABM20-A-C
UPC	074983713561

### Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie Mount



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Package	500
Weight Per each	0.002

## Uses, Certifications, and Standards

Application	Indoor;Right Angle Mounts Holds Cable Bundles Away from the Sharp Edges of Bulkheads or Cabinet Holes. Can Also be used to Mount Cable Bundles Adjacent to Any Surface
Mounting standard	Adhesive Tape CE Compliant,RoHS Compliant