

Kellems® Wire Management Products
Straight Male Cord Connectors
Cord Connectors

HUBBELL

Features

- Nylon cord connectors resist corrosion
- Tapered interior seats the bushing evenly for a liquidtight seal
- The connector body is a one-piece design with machined threads

Ordering Information

Description	Color Code	UPC	Catalog Number
Cord Connectors, Straight Male, Nylon, Gray	Blue	783585208077	SHC1035CR



Listings

CSA Certified
United States Coast Guard Approved, Title 46-Part 111
UL Listed in accordance with Standard 514B for indoor/outdoor use

Online Resources

[eCatalog](#)

Specifications

Material	Gray Nylon
Form Size	F3
NPT Hub Size	3/4 Inch
Cord Diameter Range Inches (mm)	.38"-.50" (9.5-12.7)

Performance

Environmental

Flammability	UL 94-V2
Hazardous Locations	Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
Operating Temperatures	-30°F to +225°F (-34°C to +107°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Kellems® Wire Management Products
Straight Male Cord Connectors
Cord Connectors

HUBBELL

Features

- Nylon cord connectors resist corrosion
- Tapered interior seats the bushing evenly for a liquidtight seal
- The connector body is a one-piece design with machined threads

Ordering Information

Description	Color Code	UPC	Catalog Number
Cord Connectors, Straight Male, Nylon, Gray	Blue	783585208077	SHC1035CR



Listings

CSA Certified
United States Coast Guard Approved, Title 46-Part 111
UL Listed in accordance with Standard 514B for indoor/outdoor use

Online Resources

[eCatalog](#)

Specifications

Material	Gray Nylon
Form Size	F3
NPT Hub Size	3/4 Inch
Cord Diameter Range Inches (mm)	.38"-.50" (9.5-12.7)

Performance

Environmental

Flammability	UL 94-V2
Hazardous Locations	Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
Operating Temperatures	-30°F to +225°F (-34°C to +107°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

