

Kellems® Wire Management Products

Straight Male Cord Connectors

Cord Connectors

HUBBELL

Features

- Nylon cord connectors resist corrosion
- Tapered interior seats the bushing evenly for a liquidtight seal
- The connector body is a one-piece design with machined threads

Ordering Information

| Description | Color Code | UPC | Catalog Number |
|---|------------|--------------|----------------|
| Cord Connectors, Straight Male, Nylon, Gray | Brown | 783585208084 | SHC1036CR |



Listings

CSA Certified
United States Coast Guard Approved, Title 46-Part 111
UL Listed in accordance with Standard 514B for indoor/outdoor use

Online Resources

[eCatalog](#)

Specifications

| | |
|------------------------------------|-----------------------|
| Material | Gray Nylon |
| Form Size | F3 |
| NPT Hub Size | 3/4 Inch |
| Cord Diameter Range Inches (mm) | .50"-.63" (12.7-15.9) |

Performance

Environmental

| | |
|------------------------|--|
| Flammability | UL 94-V2 |
| Hazardous Locations | Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC |
| Operating Temperatures | -30°F to +225°F (-34°C to +107°C) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Kellems® Wire Management Products

Straight Male Cord Connectors

Cord Connectors

HUBBELL

Features

- Nylon cord connectors resist corrosion
- Tapered interior seats the bushing evenly for a liquidtight seal
- The connector body is a one-piece design with machined threads

Ordering Information

| Description | Color Code | UPC | Catalog Number |
|---|------------|--------------|----------------|
| Cord Connectors, Straight Male, Nylon, Gray | Brown | 783585208084 | SHC1036CR |



Listings

CSA Certified
United States Coast Guard Approved, Title 46-Part 111
UL Listed in accordance with Standard 514B for indoor/outdoor use

Online Resources

[eCatalog](#)

Specifications

| | |
|------------------------------------|-----------------------|
| Material | Gray Nylon |
| Form Size | F3 |
| NPT Hub Size | 3/4 Inch |
| Cord Diameter Range Inches (mm) | .50"-.63" (12.7-15.9) |

Performance

Environmental

| | |
|------------------------|--|
| Flammability | UL 94-V2 |
| Hazardous Locations | Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC |
| Operating Temperatures | -30°F to +225°F (-34°C to +107°C) |

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

