

Kellems® Wire Management Products  
Straight Male Cord Connectors  
Cord Connectors

# HUBBELL

## Features

- Nylon cord connectors resist corrosion
- Tapered interior seats the bushing evenly for a liquidtight seal
- The connector body is a one-piece design with machined threads

## Ordering Information

Description	Color Code	UPC	Catalog Number
Cord Connectors, Straight Male, Nylon, Gray	Yellow	783585208091	SHC1037CR



## Listings

CSA Certified  
United States Coast Guard Approved, Title 46-Part 111  
UL Listed in accordance with Standard 514B for indoor/outdoor use

## Online Resources

[eCatalog](#)

## Specifications

Material	Gray Nylon
Form Size	F3
NPT Hub Size	3/4 Inch
Cord Diameter Range Inches (mm)	.63"-.75" (15.9-19.0)

## Performance

### Environmental

Flammability	UL 94-V2
Hazardous Locations	Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
Operating Temperatures	-30°F to +225°F (-34°C to +107°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



Kellems® Wire Management Products  
Straight Male Cord Connectors  
Cord Connectors

# HUBBELL

## Features

- Nylon cord connectors resist corrosion
- Tapered interior seats the bushing evenly for a liquidtight seal
- The connector body is a one-piece design with machined threads

## Ordering Information

Description	Color Code	UPC	Catalog Number
Cord Connectors, Straight Male, Nylon, Gray	Yellow	783585208091	SHC1037CR



## Listings

CSA Certified  
United States Coast Guard Approved, Title 46-Part 111  
UL Listed in accordance with Standard 514B for indoor/outdoor use

## Online Resources

[eCatalog](#)

## Specifications

Material	Gray Nylon
Form Size	F3
NPT Hub Size	3/4 Inch
Cord Diameter Range Inches (mm)	.63"-.75" (15.9-19.0)

## Performance

### Environmental

Flammability	UL 94-V2
Hazardous Locations	Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
Operating Temperatures	-30°F to +225°F (-34°C to +107°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

