



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SG3N0025LE D16 SNTL-G3 1PH 25KVA 240X480-120/240V AI 60HZ 150 *Hammond Power Solutions*

| | |
|------------------|---|
| Catalog Number | SG3N0025LE |
| Manufacturer | Hammond Power Solutions |
| Description | 600V Class Single Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 240X480 PV, 120/240 SV, 25 Kva, 1PH, Aluminum Wound |
| Weight per unit | 210.0 (lbs/each) |
| Product Category | 20170612135628 |

Features

| | |
|-------------------|------------------|
| kva rating | 25 |
| Number of Taps | ST-20 compliant |
| Phase | N- 1PH Dual-Dual |
| Primary Voltage | 240x480 |
| Secondary Voltage | 120/240 |

Dimensions and Weight

| | |
|--------|------|
| Height | 26.7 |
| Length | 23.8 |
| Width | 22.3 |

Descriptions

| | |
|------------------------|--|
| Description | D16 SNTL-G3 1PH 25KVA 240X480-120/240V AL 60HZ 150 |
| extra long description | HMND SG3N0025LE D16/NRC19 1PH 25kVA |
| Features | Optional infrared windows available |
| Long Description | 600V Class Single Phase DOE2016 and NRCan 2019 Compliant Energy Efficient Distribution Transformer, 240x480 PV, 120/240 SV, 25 kVA, 1PH, Aluminum Wound |
| Product Type | D16/NRC19 1PH 25KVA 240X480 120/240val |
| Special Features | Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | HPS |
| GTIN | 00803423140649 |
| Manufacturers Part Number | SG3N0025LE |
| UPC | 803423140649 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | 1 PHASE TRANSFORMERS |
| Type | Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Single Phase |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 210 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Application | General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems. |
| Enclosure | NH6-N3R - Indoor or Outdoor |
| Frequency Rating | 60 |
| Mounting standard | Floor or Wall mount CSA, UL |
| Temperature Rating | Typical 30 Average/ 40 Maximum |