

# Eaton SHB0N12

Catalog Number: SHB0N12

Eaton rotary disconnect front and right external selector handle,Front and right external handle,Front and right external selector handle,16-100A,Black,NEMA 3R/12,External handles,NEMA 3R/12,R9,Handle type: SH0,Black

Photo is representative



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton rotary disconnect external selector handle	SHB0N12
	<b>UPC</b>
	786685403571
<b>Product Length/Depth</b>	<b>Product Height</b>
1.57 in	1.06 in
<b>Product Width</b>	<b>Product Weight</b>
1.1 in	0.2 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Color

Black

### Enclosure

NEMA 3R, NEMA 12

### Handle color

Black

### Series

R9

### Type

Front and right external selector handle

## Performance Ratings

### Amperage Rating

16-100A

### Rating

NEMA 3R, NEMA 12

## Miscellaneous

### Product Category

External handles

### Special features

Front and right external handle

### Used with

Handle type: SH0

## Resources

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - SHB0N12](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton SHB0N12

Catalog Number: SHB0N12

Eaton rotary disconnect front and right external selector handle,Front and right external handle,Front and right external selector handle,16-100A,Black,NEMA 3R/12,External handles,NEMA 3R/12,R9,Handle type: SH0,Black

Photo is representative



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton rotary disconnect external selector handle	SHB0N12
	<b>UPC</b>
	786685403571
<b>Product Length/Depth</b>	<b>Product Height</b>
1.57 in	1.06 in
<b>Product Width</b>	<b>Product Weight</b>
1.1 in	0.2 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Color

Black

### Enclosure

NEMA 3R, NEMA 12

### Handle color

Black

### Series

R9

### Type

Front and right external selector handle

## Performance Ratings

### Amperage Rating

16-100A

### Rating

NEMA 3R, NEMA 12

## Miscellaneous

### Product Category

External handles

### Special features

Front and right external handle

### Used with

Handle type: SH0

## Resources

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - SHB0N12](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)