



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SKAB250 250MCM Al/Cu Butt Splice

*Nsi Industries*

Catalog Number	SKAB250
Manufacturer	Nsi Industries
Description	Easy-Splice Dual Rated Direct Burial Butt Splice Kit For 1/0 Awg to 250 MCM Utilizing A Mechanical Dual Rated Splice and Matched Heavy Wall Heat Shrink Tubing to Create An Insulated Splice For Copper and/or Aluminum Cables. Temperature Rating: 105 Degrees C. 600 Volt Maximum.
Weight per unit	0.3760 (lbs/each)
Product Category	Splicing & Terminating Kits

### Features

Cable Size	1/0 AWG-250 MCM
Cable Type	Class A-B
insulation	Heat Shrink
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Black
-------	-------

### Descriptions

Description	250MCM AL/CU BUTT SPLICE
extra long description	NSI SKAB-250 Easy Splice ALCU Butt
Features	Easy-Splice Dual Rated Direct Burial Butt Splice Kit for 1/0 AWG to 250 MCM Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating: 105 degrees C. 600 Volt Maximum.
Long Description	Easy-Splice Dual Rated Direct Burial Butt Splice Kit for 1/0 AWG to 250 MCM Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating: 105 degrees C. 600 Volt Maximum.
Product Type	Easy Splice Alcu Butt Splice 250
Special Features	Dual Rated For Use With Copper And Aluminum Cable

### Manufacturer Information

Brand	NSi
GTIN	00662381169167
Manufacturers Part Number	SKAB-250
UPC	662381169167

### Taxonomies, Classifications, and Categories

Type	Direct Burial Splice Kit With Heat Shrink
------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.376

## Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature	-40 C To 90 C