

SL35911 -- Nickel Anti-Seize Lubricating Compound, 8 Wt Oz



Product Description

Sta-Lube Nickel Anti-Seize is a nickel based formula that is free of copper, lead, sulfides and chlorides. This premium quality lubricant has extremely high temperature and excellent chemical resistance.

Product Specifications

Applications

Catalyst beds, reaction chambers, special alloy fittings. May be used on fittings, bushings, flanges, headers, nuts, screws, studs, threaded surfaces, pipes, plugs, and manifolds to prevent seizing and galling of surfaces.

Unit Package Description

8 Ounce Brush-Top Bottle

Brand

Sta-Lube

Generic Description 1

General Purpose Anti Seize Lubricant

Net Fill

8 Wt Oz

UPC Code

0 72213 35911 4

Unit Dimensions-Inches

4.25H x 2.5W x 2.5D

Units Per Case

12

Case Dimensions-Inches

5H x 6.63W x 10D

Cases Per Pallet

108

Lbs. Per Case

8

I 2 of 5 Code

30072213359115

Appearance

Silver Semi-Solid Paste

Odor

Petroleum

Base Type

Nickel

Flashpoint - TCC Method

430°F

Specific Gravity

1.24

Flammability

Non-flammable

Plastic Safe

Yes

Film Type

Wet

Evaporation Rate

<0.01 (Butyl Acetate=1)

Working Temp [Degrees F]

-95 to 2400°F

Propellant

None

NSF Registered

No

DOT Proper Shipping Name

Not Regulated

VOC % (Federal)

0

VOC g/L (Federal)

0

VOC Lbs./Gal. (Federal)

0

VOC Compliant For CA

Not Regulated

**VOC Compliant For OTC/
LADCO**

Not Regulated

VOC Category/Limit

Not Regulated

Removal (How To)

Remove with general purpose degreaser.

SL35911 -- Nickel Anti-Seize Lubricating Compound, 8 Wt Oz



Product Description

Sta-Lube Nickel Anti-Seize is a nickel based formula that is free of copper, lead, sulfides and chlorides. This premium quality lubricant has extremely high temperature and excellent chemical resistance.

Product Specifications

Applications

Catalyst beds, reaction chambers, special alloy fittings. May be used on fittings, bushings, flanges, headers, nuts, screws, studs, threaded surfaces, pipes, plugs, and manifolds to prevent seizing and galling of surfaces.

Unit Package Description

8 Ounce Brush-Top Bottle

Brand

Sta-Lube

Generic Description 1

General Purpose Anti Seize Lubricant

Net Fill

8 Wt Oz

UPC Code

0 72213 35911 4

Unit Dimensions-Inches

4.25H x 2.5W x 2.5D

Units Per Case

12

Case Dimensions-Inches

5H x 6.63W x 10D

Cases Per Pallet

108

Lbs. Per Case

8

I 2 of 5 Code

30072213359115

Appearance

Silver Semi-Solid Paste

Odor

Petroleum

Base Type

Nickel

Flashpoint - TCC Method

430°F

Specific Gravity

1.24

Flammability

Non-flammable

Plastic Safe

Yes

Film Type

Wet

Evaporation Rate

<0.01 (Butyl Acetate=1)

Working Temp [Degrees F]

-95 to 2400°F

Propellant

None

NSF Registered

No

DOT Proper Shipping Name

Not Regulated

VOC % (Federal)

0

VOC g/L (Federal)

0

VOC Lbs./Gal. (Federal)

0

VOC Compliant For CA

Not Regulated

**VOC Compliant For OTC/
LADCO**

Not Regulated

VOC Category/Limit

Not Regulated

Removal (How To)

Remove with general purpose degreaser.