



SN SERIES NUT, 1/4" ROD

CATALOG NUMBER

SN25



FEATURES

Allows side mounting of nut to threaded rod

Reduces the need for threading compared to standard nuts and washers

Ideal for retrofit projects, such as trapeze installations, where disassembly of the support system is not desired

Works with slightly damaged threads and minor burrs on the threaded rod

Reduces installation time up to 50%

PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized


Rod Size (RS): 1/4

A: 0.55"

B: 5/8"

Static Load (F): 500 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER



SN SERIES NUT, 1/4" ROD

CATALOG NUMBER

SN25



FEATURES

Allows side mounting of nut to threaded rod

Reduces the need for threading compared to standard nuts and washers

Ideal for retrofit projects, such as trapeze installations, where disassembly of the support system is not desired

Works with slightly damaged threads and minor burrs on the threaded rod

Reduces installation time up to 50%

PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized


Rod Size (RS): 1/4

A: 0.55"

B: 5/8"

Static Load (F): 500 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER