

# Eaton SP1-208Y

Catalog Number: SP1-208Y

Eaton Innovative Technology Protector surge protective device, Surge Protection Device, SP1 series, 50 kAIC, 120/208 wye, 300 L-L, 150 L-N operating voltage, Three-phase

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton SP1 surge protective device	SP1-208Y
<b>UPC</b>	<b>Product Length/Depth</b>
786685448336	2.5 in
<b>Product Height</b>	<b>Product Width</b>
4.8 in	2.9 in
<b>Product Weight</b>	<b>Warranty</b>
1.25 lb	2 year
<b>Certifications</b>	
UL 1449	

## Electrical properties

### Voltage rating

120/208 wye

### Phase

Three-phase

## Physical properties

### Type

SP1

## Resources

### Installation instructions

[SP1 Surge Protective Device Installation and Operation](#)

### Specifications and datasheets

[Eaton Specification Sheet - SP1-208Y](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton SP1-208Y

Catalog Number: SP1-208Y

Eaton Innovative Technology Protector surge protective device, Surge Protection Device, SP1 series, 50 kAIC, 120/208 wye, 300 L-L, 150 L-N operating voltage, Three-phase

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton SP1 surge protective device	SP1-208Y
<b>UPC</b>	<b>Product Length/Depth</b>
786685448336	2.5 in
<b>Product Height</b>	<b>Product Width</b>
4.8 in	2.9 in
<b>Product Weight</b>	<b>Warranty</b>
1.25 lb	2 year
<b>Certifications</b>	
UL 1449	

## Electrical properties

### Voltage rating

120/208 wye

### Phase

Three-phase

## Physical properties

### Type

SP1

## Resources

### Installation instructions

[SP1 Surge Protective Device Installation and Operation](#)

### Specifications and datasheets

[Eaton Specification Sheet - SP1-208Y](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)