



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SS403 3WAY In-Wall Dig TMR

Nsi Industries

Catalog Number	SS403
Manufacturer	Nsi Industries
Description	Interval Timer 24 HR 120-277V White
Weight per unit	0.3900 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPST
Base	Screw
Contact Rating	120-230-277 VAC
Phase	Single Phase
Poles	1
Timing Range	7 DAY

Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------

Descriptions

Description	3WAY IN-WALL DIG TMR
extra long description	TORK SS403 Interval Timer 24 Hr 120
Features	Tork Digital Interval Timer w/o Neutral APPLICATIONS: Offices, Meeting Rooms, Energy Code Timed Override, Exhaust Fans, Equipment Rooms, Closets, Storage Spaces. FEATURES: COLOR: White (single gang decorator wall plate included) ENERGY CODE PRESET: 2 hour timing for Title 24 and IECC (default) 4 hour timing for ASHRAE 90.1 (with quick dip switch adjustment) PROGRAMMABLE: 5 minutes to 25 hour: 5 minute steps from 5 minutes to 1 hour 10 minute steps from 1 to 4 hours 30 minute steps from 4 to 12 hours 1 hour
Long Description	Interval Timer 24 Hr 120-277V White
Product Type	Interval Timer 24 HR 120-277V White
Special Features	White 7 Day In Wall Time Switch

Manufacturer Information

Brand	NSi
GTIN	00786261140296
Manufacturers Part Number	SS403
UPC	786261140296

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Digital Auto Off In Wall Time Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.39

Uses, Certifications, and Standards

Application	NSI
environmental conditions	32 - + 104 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	32 - + 104 F
standard	cULus