



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SS6 Smooth 302SS 6G Toggle

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | SS6 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Smooth Metal Wall Plate, 6-Gang Toggle, 302/304 Stainless Steel |
| Weight per unit | 0.5200 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|---------------|
| cutout | Toggle |
| indoor/outdoor | Indoor |
| insulation | Bare |
| media | Yes |
| Mounting Type | Strap Mounted |
| Number of Gangs | 6 |
| orientation | Vertical |
| Wall Plate Type | Toggle Switch |

Material, Color, and Finish

| | |
|--------|----------|
| Finish | Metallic |
|--------|----------|

Dimensions and Weight

| | |
|-----------|-------|
| Size | 7" |
| Thickness | 0.032 |

Descriptions

| | |
|------------------------|---|
| Description | SMOOTH 302SS 6G TOGGLE |
| extra long description | P&S SS6 SMOOTH 302SS 6G TOGGLE |
| Long Description | Smooth Metal Wall Plate, 6-Gang Toggle, 302/304 Stainless Steel |
| Product Type | Smooth 302SS 6G Toggle |
| Special Features | Stainless steel, non magnetic, appealing finish. |

Manufacturer Information

| | |
|-------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007129076 |
| UPC | 785007129076 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | Residential cord connectors |
| Type | Wall Plate |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.52 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | CULUS, CSA, UL, CSA |