

# Specifications



Photo is representative

## Eaton STL131A120CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, 13-jaw, Pre-wired test switch, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	STL131A120CH
<b>UPC</b>	786685703404
<b>PRODUCT LENGTH/DEPTH</b>	5.3 in
<b>PRODUCT HEIGHT</b>	21.8 in
<b>PRODUCT WIDTH</b>	12.6 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Austin Energy Approved, transformer rated



### Product specifications

<b>TYPE</b>	Transformer rated socket
-------------	--------------------------

### Resources

<b>AMPERAGE RATING</b>	20A
<b>FEED TYPE</b>	Bottom
<b>NUMBER OF JAWS</b>	13-jaw
<b>VOLTAGE RATING</b>	600 V
<b>ACCESSORIES</b>	Pre-wired test switch
<b>NUMBER OF SOCKETS</b>	1

**SPECIFICATIONS AND DATASHEETS**

[Eaton Specification Sheet - STL131A120CH](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications



Photo is representative

## Eaton STL131A120CH

Eaton meter socket, Transformer rated socket, 20A, Under, Solid top, 13-jaw, Pre-wired test switch, 600 Vac

### General specifications

<b>PRODUCT NAME</b>	Eaton meter socket
<b>CATALOG NUMBER</b>	STL131A120CH
<b>UPC</b>	786685703404
<b>PRODUCT LENGTH/DEPTH</b>	5.3 in
<b>PRODUCT HEIGHT</b>	21.8 in
<b>PRODUCT WIDTH</b>	12.6 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Austin Energy Approved, transformer rated



### Product specifications

<b>TYPE</b>	Transformer rated socket
-------------	--------------------------

### Resources

<b>AMPERAGE RATING</b>	20A
<b>FEED TYPE</b>	Bottom
<b>NUMBER OF JAWS</b>	13-jaw
<b>VOLTAGE RATING</b>	600 V
<b>ACCESSORIES</b>	Pre-wired test switch
<b>NUMBER OF SOCKETS</b>	1

---

**SPECIFICATIONS AND DATASHEETS**

---

[Eaton Specification Sheet - STL131A120CH](#)

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

