



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## T68 2" Cond Body *Appleton/Oz Gedney*

Catalog Number	T68
Manufacturer	Appleton/Oz Gedney
Description	FM8 Grayloy-Iron Unilets Type T Conduit Outlet Body, Hub Size: 2 In, Form: 8, Length: 12.38 In, Width: 5.13 In, Height: 3.56 In, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate and Epoxy Powder Coat), Color: Gray, Con
Weight per unit	8.7 (lbs/each)
Product Category	Bodies & Covers

### Features

connection	Tapered Female Threaded
Form	8

### Material, Color, and Finish

Color	Gray
Finish	Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat)

### Dimensions and Weight

Height	3.56
Hub Size	2
Length	12.38
Width	5.13

### Descriptions

Description	2" COND BODY
extra long description	APP T68 2 TYPE T FORM 8 BODY
Long Description	FM8 Grayloy-Iron UNILETS Type T Conduit Outlet Body, Hub Size: 2 IN, Form: 8, Length: 12.38 IN, Width: 5.13 IN, Height: 3.56 IN, Material: Grayloy-Iron, Finish: Triple-Coat (Zinc Electroplate, Chromate And Epoxy Powder Coat), Color: Gray, Con
Product Type	2 Type T Form 8 Body
Special Features	Accurately tapped, tapered threads for tight, rigid joints and excellent ground continuity;Allow connections for branch runs;Completely interchangeable with Crouse-Hinds Form 8 bodies, gaskets and covers;Connect and change direction of conduit runs;Equivalent FM8 and Form 8 units have identical applications and installation dimensions;Fits flush and snug against flat surfaces for more stable installation;Flat back design provides greater cubic content for easier wire pulling and more room for splicing;Make



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Appleton
GTIN	00781381744362
UPC	781381744362

## Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Type T Conduit Outlet Body

## Packaging

Carton	1
Weight Per each	8.7

## Uses, Certifications, and Standards

Application	For Use With Rigid Steel Conduit And IMC
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1