



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## T8H04096GFA8840D 40W Led T8 96" 40K DBL End 120/277V SNGL Pin Glass *Rab Lighting*

Catalog Number	T8H04096GFA8840D
Manufacturer	Rab Lighting
Description	Linear Tubes 5500 Lumens T8HO 40W Base Field Adjustable Power 4000K Double Ended Wiring Method
Weight per unit	0.8800 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Ballast Type	Double Ended power Type B tubes
Base	Fa8
beam angle	210
Fixture Type	Linear Tubes
lumens	5500
Shape	T8
total harmonic distortion	=20+5%
Voltage Rating	120-277
Wattage	40

### Material, Color, and Finish

Color	White
color rendering index (cri)	82
color temperature	4000
Finish	Matte

### Dimensions and Weight

Length	93.7
--------	------

### Descriptions

Description	40W LED T8 96" 40K DBL END 120/277V SNGL PIN GLASS
extra long description	RAB T8HO-40-96G-FA8-840-DE-BYP LED
Long Description	LINEAR TUBES 5500 LUMENS T8HO 40W BASE FIELD ADJUSTABLE POWER 4000K DOUBLE ENDED WIRING METHOD

Product Type	Led T8 8FT Glass T-B De 40W 4K Fa8
--------------	------------------------------------

Special Features	Replacement for conventional fluorescent T8 and T12 linear tubesIntegral Driver enables lamp to be wired directly to line voltage without need for an external driver or ballastDouble ended wiring methodWorks with shunted sockets.Approximately 50% more energy efficient when compared to Fluorescent T8 lamps50,000 hour Lifespan.Rated for use in enclosed and open fixtures in dry or damp locationsDiffused frosted lens will maintain the same light quality over timeInstant on full brightnessEnvironmentally friend
------------------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00192552006156
Manufacturers Part Number	T8HO-40-96G-FA8-840-DE-BYP
UPC	192552006156

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Tubes

## Packaging

Carton	1
Package	10
Weight Per each	0.88

## Uses, Certifications, and Standards

Application	Indoor Lamps
-------------	--------------