



**Thermal  
T&B Catalog Number:**

TA25DU32

**UPC Number:**

66201988556

**Status:**

Active

**Description:**

3 pole thermal overload relay with 24-32 amp setting range

**Features**

Economic overload protection

Comes with RESET, TEST, and STOP functions

Automatic and manual reset

**Application**

Offers reliable protection for motors in the event of overload or phase failure

For use with single and three phase motors

**General**

Series TA25DU

Poles 3

For Contactors A/E/L9 through A/E/L40 and A/E/L9N00 through A/E/L26N1

Output Contacts 1 NC and 1 NO

Trip Class 10A

Reset Type Manual/Automatic

**Dimension Information**

H x W x D (inches) 3.70 x 1.73 x 3.70

**Specifications**

Amp Setting Range (A) 24-32

**Packaging**

T&B Inner Pack 1

Package in Units 48

T&B Sold in UOM Each

T&B Weight Per UOM 0.48 lbs. Each

**Certifications**

Approvals UL, CSA, CE

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com



**Thermal  
T&B Catalog Number:**

TA25DU32

**UPC Number:**

66201988556

**Status:**

Active

**Description:**

3 pole thermal overload relay with 24-32 amp setting range

**Features**

Economic overload protection

Comes with RESET, TEST, and STOP functions

Automatic and manual reset

**Application**

Offers reliable protection for motors in the event of overload or phase failure

For use with single and three phase motors

**General**

|                 |  |
|-----------------|--|
| Series          | TA25DU   |
| Poles           | 3  |
| For Contactors  | A/E/L9 through A/E/L40 and A/E/L9N00 through A/E/L26N1 |
| Output Contacts | 1 NC and 1 NO  |
| Trip Class      | 10A  |
| Reset Type      | Manual/Automatic                                       |

**Dimension Information**

H x W x D (inches) 3.70 x 1.73 x 3.70

**Specifications**

Amp Setting Range (A) 24-32

**Packaging**

|                    |                |
|--------------------|----------------|
| T&B Inner Pack     | 1              |
| Package in Units   | 48             |
| T&B Sold in UOM    | Each           |
| T&B Weight Per UOM | 0.48 lbs. Each |

**Certifications**

Approvals UL, CSA, CE

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com