



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **TC161PR 16G 1PR VNTC 600V** *Southwire Company*

Catalog Number	TC161PR
Manufacturer	Southwire Company
Description	Control Cable, TC, TFFN Type; 1000 FT; 0.28 Inch Outer Diameter; Annealed Bare Copper Conductor Material; UI 1277, UI 1685 Approval; 600 V Voltage Rating; 75 Deg C (Wet), 90 Deg C (Dry) Temperature Rating; 2 Conductor(S); PVC/Nylon Insulation Material
Weight per unit	0.0500 (lbs/ft)
Product Category	20100927141952

### **Features**

Conductor Size	16 AWG
Number of Conductors	2
Shielding Type	Non-Shielded
Stranding	7 STRANDS
Voltage Rating	600 V

### **Material, Color, and Finish**

Conductor Material	ANNEALED BARE COPPER
Insulation Material	PVC/Nylon
Jacket Color	BLACK
Jacket Material	PVC

### **Dimensions and Weight**

Length	1000 ft
Outer Diameter	0.28 Inch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	ROHS Compliant; Applicable Standard NFPA 70, NEC, ASTM, ICEA S-58-679
Commodity Description	600v Shielded Tray Cable - Sdt - Tc
Description	16G 1PR VNTC 600V
extra long description	TC, TFFN TYPE; 1000 FT; 0.28 INCH OUTER DIAMETER; ANNEALED BARE COPPER CONDUCTOR MATERIAL; UL 1277, UL 1685 APPROVAL; 600 V VOLTAGE RATING; 75 DEG C (WET), 90 DEG C (DRY) TEMPERATURE RATING; 2 CONDUCTOR(S); PVC/NYLON INSULATION MATERIAL; 16 AWG CONDUCTOR SIZE; PVC JACKET MATERIAL; REEL PACKAGE TYPE; 7 STRANDS STRANDING; BLACK JACKET COLOR; NON-SHIELDED SHIELDING TYPE; ROHS COMPLIANT; APPLICABLE STANDARD NFPA 70, NEC, ASTM, ICEA S-58-679
Long Description	CONTROL CABLE, TC, TFFN TYPE; 1000 FT; 0.28 INCH OUTER DIAMETER; ANNEALED BARE COPPER CONDUCTOR MATERIAL; UL 1277, UL 1685 APPROVAL; 600 V VOLTAGE RATING; 75 DEG C (WET), 90 DEG C (DRY) TEMPERATURE RATING; 2 CONDUCTOR(S); PVC/NYLON INSULATION MATERIAL
Product Type	Control Cable

## Manufacturer Information

Brand	Copper
Manufacturers Part Number	57788302

## Taxonomies, Classifications, and Categories

Category Description	TRAY CABLE
Type	TC, TFFN

## Availability

Manufacturer Status	Non-Stock
---------------------	-----------

## Packaging

Carton	1
Package	1000
Package Type	Reel
Weight Per foot	0.05

## Uses, Certifications, and Standards

Approval	UL 1277, UL 1685
Temperature Rating	75 DEG C (WET), 90 DEG C (DRY)