



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TC345A 4WAYADH MTG Base 1.13X1.13 Nat Nyl

Abb Installation Products, Inc

| | |
|------------------|---|
| Catalog Number | TC345A |
| Manufacturer | Abb Installation Products, Inc |
| Description | Four-Way Adhesive Mounting Base, Natural Nylon 6.6 For Temperatures Up to 66 Degrees Celsius (150 F), Length Of 28.6MM (1.13 Inches), Width Of 28.6MM (1.13 Inches), Self-Adhesive Mounting Method, Bulk Pack |
| Weight per unit | 0.0010 (lbs/each) |
| Product Category | Cable Ties & Wraps |

Features

| | |
|----------|---------------------|
| Material | Nylon/Polyamide 6.6 |
|----------|---------------------|

Material, Color, and Finish

| | |
|-------|---------|
| Color | Natural |
|-------|---------|

Descriptions

| | |
|------------------------|---|
| Description | 4WAYADH MTG BASE 1.13X1.13 NAT NYL |
| extra long description | ABB TC345A 4WAYADH MTG BASE 1.13X1 |
| Long Description | Four-Way Adhesive Mounting Base, Natural Nylon 6.6 for Temperatures up to 66 Degrees Celsius (150 F), Length of 28.6mm (1.13 Inches), Width of 28.6mm (1.13 Inches), Self-Adhesive Mounting Method, Bulk Pack |
| Product Type | 4WAYADH MTG Base 1.13X1.13 Nat Nyl |
| Special Features | Eliminates errors in premounting the base with respect to its orientation to wire bundle direction |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ty-Rap |
| GTIN | 00786210868042 |
| Manufacturers Part Number | TC345A |
| UPC | 786210868042 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
| Type | MOUNTING BASE |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 1000 |
| Weight Per each | 0.001 |

Uses, Certifications, and Standards

| | |
|-----------------------|---------------|
| Mounting | Self-Adhesive |
| Operating Temperature | -32 to +150 F |