

Specifications

Eaton TCI143

Eaton strain relief dust tight grip, Insulated, 0.40-0.54" cord diameter, 1/2" fitting, NPT thread

General specifications

PRODUCT NAME	Eaton strain relief dust tight grip
CATALOG NUMBER	TCI143
UPC	040893646510
PRODUCT LENGTH/DEPTH	0.922 in
PRODUCT HEIGHT	8.177 in
PRODUCT WIDTH	1.034 in
PRODUCT WEIGHT	0.065 lb
CERTIFICATIONS	CSA Certified UL Listed



Product specifications

SPECIAL FEATURES	Insulated
TYPE	Strain relief dust tight grip
CORD DIAMETER	0.40-0.54 in
FITTING SIZE	1/2 in
THREAD TYPE	NPT

Resources

CATALOGS	Arrow Hart Buyers Guide Section N
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TCI143

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton TCI143

Eaton strain relief dust tight grip, Insulated, 0.40-0.54" cord diameter, 1/2" fitting, NPT thread

General specifications

PRODUCT NAME	Eaton strain relief dust tight grip
CATALOG NUMBER	TCI143
UPC	040893646510
PRODUCT LENGTH/DEPTH	0.922 in
PRODUCT HEIGHT	8.177 in
PRODUCT WIDTH	1.034 in
PRODUCT WEIGHT	0.065 lb
CERTIFICATIONS	CSA Certified UL Listed



Product specifications

SPECIAL FEATURES	Insulated
TYPE	Strain relief dust tight grip
CORD DIAMETER	0.40-0.54 in
FITTING SIZE	1/2 in
THREAD TYPE	NPT

Resources

CATALOGS	Arrow Hart Buyers Guide Section N
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TCI143

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

