



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TECK0503 1/2" Alu Teck Cable Gland *Crouse-Hinds*

Catalog Number	TECK0503
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Teck Cable Gland, Teck Armoured Cable, Armoured Gland, Aluminum, Outer Sheath Min/Max: 0.72-0.88", General Purpose, 1/2" NPT, Armor Range Min/Max: 0.61-0.80"
Weight per unit	0.2700 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

Features

connection	Watertight seal on outer sheath of cable
dimensions	2.9300 IN X 1.6000 IN X 1.6000 IN
Material	Aluminum

Material, Color, and Finish

Color	Grey
-------	------

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Description	1/2" ALU TECK CABLE GLAND
extra long description	CRS-H TECK050 3 1/2 AL FT TECK CAB
Features	TECK cable glands from Eaton Crouse-Hinds Division are listed for use with TECK corrugated cable, or interlocked steel or aluminum cable. TECK glands provide a means to terminate at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution equipment. TECK cable glands form a Type 4, IP56 watertight seal around the cable and at enclosure entry, and they provide excellent cable pull-out protection exceeding CSA requirements.
Long Description	Eaton Crouse-Hinds series TECK cable gland, TECK armoured cable, Armoured gland, Aluminum, Outer sheath min/max: 0.72-0.88", General purpose, 1/2" NPT, Armor range min/max: 0.61-0.80"
Product Type	1/2 AI FT Teck Cab Jack Od 0.725-0.885
Special Features	TECK CAB JACKET OD 0.525 - 0.650

Manufacturer Information

Brand	Eaton
GTIN	00782274116679
Manufacturers Part Number	TECK050 3
UPC	782274116679



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland

Packaging

Carton	1
Package	20
Weight Per each	0.27

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	CSA
Temperature Rating	-25 degrees C to 60 degrees C