

# Specifications



## Eaton TCFH100N

Eaton Bussmann series TCFH modular fuse holder, Electrical panelboards, Machinery disconnects, Industrial control, Required finger safe systems, 100 A, Class CF, Glass filled PBT, Panel, 600 Vac/dc, Low-peak finger safe fuse

### General specifications

PRODUCT NAME	Eaton Bussmann series TCFH modular fuse holder
CATALOG NUMBER	TCFH100N
UPC	051712223508
PRODUCT LENGTH/DEPTH	2.91 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed

## Electrical rating

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac, 600 Vdc

## General information

CLASS	Class CF
MOUNTING METHOD	Panel
USED WITH	low-peak finger safe fuse

## Physical details

MATERIAL	Glass filled PBT
----------	------------------

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a>
MULTIMEDIA	<a href="#">The Power of Space</a> <a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TCFH100N</a>
TECHNICAL DATA SHEETS	<a href="#">TCFH100N~CUBFUSE 100 AMP HOLDER HIGH PROFILE</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Datasheet - FNQ-30</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TCFH100N

Eaton Bussmann series TCFH modular fuse holder, Electrical panelboards, Machinery disconnects, Industrial control, Required finger safe systems, 100 A, Class CF, Glass filled PBT, Panel, 600 Vac/dc, Low-peak finger safe fuse

### General specifications

PRODUCT NAME	Eaton Bussmann series TCFH modular fuse holder
CATALOG NUMBER	TCFH100N
UPC	051712223508
PRODUCT LENGTH/DEPTH	2.91 in
PRODUCT HEIGHT	2.1 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	0.25 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	Contact Manufacturer UL Listed

## Electrical rating

AMPERAGE RATING	100 A
VOLTAGE RATING	600 Vac, 600 Vdc

## General information

CLASS	Class CF
MOUNTING METHOD	Panel
USED WITH	low-peak finger safe fuse

## Physical details

MATERIAL	Glass filled PBT
----------	------------------

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a>
MULTIMEDIA	<a href="#">The Power of Space</a> <a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - TCFH100N</a>
TECHNICAL DATA SHEETS	<a href="#">TCFH100N~CUBFUSE 100 AMP HOLDER HIGH PROFILE</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Datasheet - FNQ-30</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

