



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



THQL2135 2POLE 35AMP Q-Line *Industrial Connections &*

Catalog Number	THQL2135
Manufacturer	Industrial Connections &
Description	Q Line Circuit Breakers Are One-Inch Wide Per Pole, Compact, Thermal-Magnetic Devices Designed For Residential and Commercial Applications In Load Centers or Lighting Panels. All Q Line Circuit Breakers Feature Quick-Make / Quick-Break Mechanisms, Common Trip Bars, and Easy to Spot Trip Indication to Ensure Safety and Reliability. Q Line Breakers Can Be Ordered With Auxiliary Contact and Shunt Trip Accessories, and Can Be Ordered For Use In Hid Applications. The THQL2135 Breaker Features 2 Poles. An Ampere
Weight per unit	650.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	35 A
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
Poles	2
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	120/240 V



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	2POLE 35AMP Q-LINE
extra long description	GE THQL2135 THQL 2POLE 120/240V 10K
Long Description	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL2135 breaker features 2 poles. an ampere
Product Type	THQL 2POLE 120/240V 10K Ic 35amp
Special Features	Q Line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications in load centers or lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. The THQL2135 breaker features 2 poles. an ampere

Manufacturer Information

Brand	GE
GTIN	00783164138337
Manufacturers Part Number	THQL2135
UPC	783164138337

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
----------------------	---

Packaging

Carton	1
Weight Per each	650

Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592