



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## THQP250 2P 50A 120/240V Tandem Breaker

*Industrial Connections &*

Catalog Number	THQP250
Manufacturer	Industrial Connections &
Description	THQP Breakers Are A Smaller, Smarter Solution For Today'S Cost- and Quality-Conscious Contractors and Homeowners. Half The Width and Identical In Design In Comparison to Standard Breakers, They Allow Use Of Smaller Load Centers and For Maximum Savings Of Space and Money. Ge Is The Only Manufacturer That Gives You This Cost Advantage Without Sacrificing Flexibility. The THQP250 Breaker Features A 1/2" Width, 2 Pole, An Ampere Rating Of 15 A, An Interrupting Rating Of 10KAIC, and A Voltage Rating Of 120/240V
Weight per unit	392.0 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

### Features

amperage rating	50 A
connection	8-4 kcmil / 8-4 kcmil
frame	Q-Line
interrupt rating	10kA@120 Vac / 10kA@120/240 Vac
Load Rating	HACR
Poles	2
trip range	Non-Interchangeable
Trip Type	LI
Voltage Rating	120/240 V



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	2P 50A 120/240V TANDEM BREAKER
extra long description	GE THQP250 THQP 2 POLE 120/240V 10K
Long Description	THQP breakers are a smaller, smarter solution for today's cost- and quality-conscious contractors and homeowners. Half the width and identical in design in comparison to standard breakers, they allow use of smaller load centers and for maximum savings of space and money. GE is the only manufacturer that gives you this cost advantage without sacrificing flexibility. The THQP250 breaker features a 1/2" width, 2 pole, an ampere rating of 15 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V
Product Type	THQP 2 Pole 120/240V 10K Ic 50amp
Special Features	THQP breakers are a smaller, smarter solution for today's cost- and quality-conscious contractors and homeowners. Half the width and identical in design in comparison to standard breakers, they allow use of smaller load centers and for maximum savings of space and money. GE is the only manufacturer that gives you this cost advantage without sacrificing flexibility. The THQP250 breaker features a 1/2" width, 2 pole, an ampere rating of 15 A, an interrupting rating of 10kAIC, and a voltage rating of 120/240V

## Manufacturer Information

Brand	GE
GTIN	00783164085778
Manufacturers Part Number	THQP250
UPC	783164085778

## Taxonomies, Classifications, and Categories

Category Description	Specialty Breakers (Quad, Dupl, Shunt Trip)
----------------------	---

## Packaging

Carton	1
Weight Per each	392

## Uses, Certifications, and Standards

Application	Thermal Magnetic
standard	E11592