



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TM870DBCC10 Radiant Switch 1P 15A 120/277V Dark Bronze

*Pass & Seymour/Legrand*

Catalog Number	TM870DBCC10
Manufacturer	Pass & Seymour/Legrand
Description	The Perfect Upgrade For Your Basic Light Switch, The Single-Pole Switch From The Radiant Registered Collection Provides On/Off Control Of A Light or Fixture From A Single Location, While Combining Clean Lines and Smooth Paddle Action For A Sophisticated Touch. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately.
Weight per unit	0.1690 (lbs/each)
Product Category	Gen Purpose Switches

### Features

Contact Rating	15 Amp, 120/125 VAC
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	1
Switch Type	Paddle
Voltage	120/277 V
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Metallic
--------	----------

### Descriptions

Description	RADIANT SWITCH 1P 15A 120/277V DARK BRONZE
extra long description	P&S TM870DBCC10 RADIANT SWITCH 1P 1
Long Description	The perfect upgrade for your basic light switch, the Single-Pole Switch from the radiant Registered Collection provides on/off control of a light or fixture from a single location, while combining clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.
Product Type	Radiant Switch 1P 15A 120/277V DRK Brnze



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007029383
Manufacturers Part Number	TM870-DBCC10
UPC	785007029383

## Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	SWITCH

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	10
Weight Per each	0.169

## Uses, Certifications, and Standards

standard	CULUS, UL
----------	-----------