



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM873 Radiant Switch 3W 15A 120/277V BN *Pass & Seymour/Legrand*

| | |
|------------------|--|
| Catalog Number | TM873 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Combination Switch, 3 Ways, 15 A, 120 to 277 V, Thermoplastic, Brass Contact Material, Brown, Grounding Connection, Wall Mount, 1.43 (L) X 1.27 (W) X 4.19 (H) In, 0.15 LB |
| Weight per unit | 0.1498 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|--------------------|--------------------|
| gang | 3 |
| indoor/outdoor | Indoor |
| insulation | Bare |
| Number of Gangs | 1.0 |
| Number of Switches | 1.0 |
| orientation | Vertical |
| Poles | 3-Way, Single Pole |
| Switch Type | Paddle |
| Voltage | 120/277 V |

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 1.8" |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | RADIANT SWITCH 3W 15A 120/277V BN |
| extra long description | P&S TM873 RADIANT SWITCH 3W 15A 120 |

Manufacturer Information

| | |
|-------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007245417 |
| UPC | 785007245417 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.1498 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| environmental conditions | 95% (relative humidity, non-condensing) |
| Mounting | WALL |
| standard | UL, CULUS, UL, cULus |