



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TM873NICC10 Decor Switch 3W 15A 120/277VAC Nickel

Pass & Seymour/Legrand

Catalog Number	TM873NICC10
Manufacturer	Pass & Seymour/Legrand
Description	Allowing Control Of A Light or Fixture From Two Separately Located Switches, The Radiant Registered 3-Way Switch Upgrades Your Space With Clean Lines and Smooth Paddle Action For A Sophisticated Touch. Made Exclusively For Use With Screwless Wall Plates From The Radiant Registered Collection, Sold Separately.
Weight per unit	0.1775 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Rating	15 Amp, 120/125 VAC
Material	Thermoplastic
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
operating cycles	50000
Poles	3-Way, 1
Switch Type	Paddle
Voltage	120/277 V
Voltage Rating	120
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Metallic
--------	----------

Dimensions and Weight

Size	1.27" Depth x 1.43" Width x 4.19" Height
------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DECOR SWITCH 3W 15A 120/277VAC NICKEL
extra long description	P&S TM873NICC10 3-WAY DECOR SW 15A
Long Description	Allowing control of a light or fixture from two separately located switches, the radiant Registered 3-Way Switch upgrades your space with clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately.
Product Type	3-Way Decor SW 15A 120/277VAC Nickel
Special Features	Everyone wants a home that's a step above ordinary. Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007021028
Manufacturers Part Number	TM873-NICC10
UPC	785007021028

Taxonomies, Classifications, and Categories

Category Description	Residential plates
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	10
Weight Per each	0.1775

Uses, Certifications, and Standards

Application	Residential
environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximun continuous +115°C, minimum -40°C
standard	CULUS, CSA Listed, UL Listed