


Specifications



Eaton TP246

Eaton Crouse-Hinds series Switch Box, (1) 1/2", S, set 7/8", 2, AC/MC clamps, 3-1/2", (1) 1/2" , Steel, (2) 1/2", Gangable, 18.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP246
UPC	786189102468
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.88 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
TYPE	Gangable
CAPACITY	18 cubic in
CONDUIT/CABLE	AC/MC clamps

BRACKET STYLE	S, Set 7/8"
END KNOCKOUTS	(1) 1/2 in
SIDE KNOCKOUTS	(2) 1/2 in
BOTTOM KNOCKOUTS	(1) 1/2 in
CABLE KNOCKOUTS	2
MATERIAL	Steel

Resources

CATALOGS [Crouse-Hinds series Steel Switch Boxes catalog page](#)

CERTIFICATION REPORTS [Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

SPECIFICATIONS AND DATASHEETS [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP246](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.


Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton TP246

Eaton Crouse-Hinds series Switch Box, (1) 1/2", S, set 7/8", 2, AC/MC clamps, 3-1/2", (1) 1/2" , Steel, (2) 1/2", Gangable, 18.0 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series switch box
CATALOG NUMBER	TP246
UPC	786189102468
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	3.5 in
PRODUCT WEIGHT	0.88 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

DEPTH	3-1/2"
TYPE	Gangable
CAPACITY	18 cubic in
CONDUIT/CABLE	AC/MC clamps

BRACKET STYLE	S, Set 7/8"
END KNOCKOUTS	(1) 1/2 in
SIDE KNOCKOUTS	(2) 1/2 in
BOTTOM KNOCKOUTS	(1) 1/2 in
CABLE KNOCKOUTS	2
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series Steel Switch Boxes catalog page
CERTIFICATION REPORTS	Steel Switch Boxes UL certification Steel Switch Boxes Canadian certification
SPECIFICATIONS AND DATASHEETS	Steel Outlet Boxes for Electrical Systems Eaton Specification Sheet - TP246

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

