



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## TP280 [25] 4 Oct Box W/BRKT *Crouse-Hinds*

Catalog Number	TP280
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Octagon Outlet Box, (5) 1/2", 4", C, 15.5 Cubic Inch Capacity
Weight per unit	33.6 (lbs/each)
Product Category	Outlet Boxes, Etc. - Steel

### Features

Cable Entry	KO
dimensions	4.0000 IN X 4.0000 IN X 1.5000 IN
Knockouts	(5) 1/2 in

### Material, Color, and Finish

Color	Colorless
-------	-----------

### Dimensions and Weight

Depth	1-1/2
Height	4
Width	4

### Descriptions

Construction	Drawn
Description	[25] 4 OCT BOX W/BRKT
extra long description	THEP TP280 4 OCT COND OUTLET BOX C
Features	Crouse-Hinds series steel octagon outlet boxes, covers, adjustable bar hangers and ceiling pans can be used in the installation of ceiling or wall lighting fixtures or as a junction box. A variety of labor-saving mounting brackets are available that allow for easy positioning of the octagon box along studs or joists. The adjustable bar hangers allow the octagon box to be located anywhere along the length of the bar.
Long Description	Eaton Crouse-Hinds series Octagon Outlet Box, (5) 1/2", 4", C, 15.5 cubic inch capacity
Product Type	4 Oct Cond Outlet Box C BRKT
Special Features	Fixture Rated, Weight 60 Lb per 100

### Manufacturer Information

Brand	Eaton
GTIN	00786189102802
Manufacturers Part Number	TP280
UPC	786189102802



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	STEEL BOXES & COVERS
Type	Octagon outlet box

## Packaging

Carton	1
Package	50
Weight Per each	33.633

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Mounting standard	C BRACKET UL, CSA