

# Specifications



## Eaton TP301

Eaton Crouse-Hinds series Ceiling Fan Box, (3) 1/2", 4", 1/2", Steel, Fan rated, fixture rated, 6.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series ceiling fan box
<b>CATALOG NUMBER</b>	TP301
<b>UPC</b>	786189103014
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.51 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>DEPTH</b>	1/2"
<b>CAPACITY</b>	6 cubic in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in

<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Fan rated, fixture rated

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification</a> <a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP301</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.



# Specifications



## Eaton TP301

Eaton Crouse-Hinds series Ceiling Fan Box, (3) 1/2", 4", 1/2", Steel, Fan rated, fixture rated, 6.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series ceiling fan box
<b>CATALOG NUMBER</b>	TP301
<b>UPC</b>	786189103014
<b>PRODUCT LENGTH/DEPTH</b>	4 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	4 in
<b>PRODUCT WEIGHT</b>	0.51 lb



Powering Business Worldwide

### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4"
<b>DEPTH</b>	1/2"
<b>CAPACITY</b>	6 cubic in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in

<b>MATERIAL</b>	Steel
<b>SPECIAL FEATURES</b>	Fan rated, fixture rated

## Resources

<b>CATALOGS</b>	<a href="#">Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page</a>
<b>CERTIFICATION REPORTS</b>	<a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification</a> <a href="#">Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Steel Outlet Boxes for Electrical Systems</a> <a href="#">Eaton Specification Sheet - TP301</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

