

Specifications

Eaton TP356

Eaton Crouse-Hinds series Adjustable Bar Hanger, Steel, Not fan rated, 16"

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series adjustable bar hanger |
| CATALOG NUMBER | TP356 |
| UPC | 786189103564 |
| PRODUCT LENGTH/DEPTH | 22.5 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.41 lb |



Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|-------------------------|---------------|
| STUD SPACING | 16" |
| MATERIAL | Steel |
| SPECIAL FEATURES | Not fan rated |

Resources

| | |
|------------------------------|--|
| CATALOGS | Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page |
| CERTIFICATION REPORTS | Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification |

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
TP356](#)

[Steel Outlet Boxes for
Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.



Specifications

Eaton TP356

Eaton Crouse-Hinds series Adjustable Bar Hanger, Steel, Not fan rated, 16"

General specifications

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Crouse-Hinds series adjustable bar hanger |
| CATALOG NUMBER | TP356 |
| UPC | 786189103564 |
| PRODUCT LENGTH/DEPTH | 22.5 in |
| PRODUCT HEIGHT | 1 in |
| PRODUCT WIDTH | 1 in |
| PRODUCT WEIGHT | 0.41 lb |



Certifications and compliances

| | |
|----------------------------|----------------------------------|
| AREA CLASSIFICATION | Ordinary/Non-Hazardous Locations |
| STANDARDS TYPE | NEC/CEC |

Product specifications

| | |
|-------------------------|---------------|
| STUD SPACING | 16" |
| MATERIAL | Steel |
| SPECIAL FEATURES | Not fan rated |

Resources

| | |
|------------------------------|--|
| CATALOGS | Crouse-Hinds series Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans catalog page |
| CERTIFICATION REPORTS | Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans Canadian certification Steel Octagon Boxes, Covers, Adjustable Bar Hangers and Ceiling Pans UL certification |

**SPECIFICATIONS AND
DATASHEETS**

[Eaton Specification Sheet -
TP356](#)

[Steel Outlet Boxes for
Electrical Systems](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights
Reserved.

Eaton is a registered trademark.

All other trademarks are property of
their respective owners.

Follow us on social media to get the latest
product and support information.

