

Eaton TP403PF

Catalog Number: TP403PF

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 1/2", (4) 1/2", (1) 3/4" E, Includes ground screw with pigtail lead, 30.3 cubic inch capacity

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP403PF
	UPC
	786189000283
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	0.84 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Capacity

30.3 cubic in

Depth

2-1/8"

Conduit/cable

Conduit (no clamps)

Construction

Welded

Side knockouts

(8) 1/2 in, (4) 1/2 in, (1) 3/4 in E

Bottom Knockouts

(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E

Material

Steel

Special features

Includes ground screw with pigtail lead

Resources

Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP403PF](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP403PF

Catalog Number: TP403PF

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", Conduit (no clamps), Welded, 2-1/8", Steel, (8) 1/2", (4) 1/2", (1) 3/4" E, Includes ground screw with pigtail lead, 30.3 cubic inch capacity

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP403PF
	UPC
	786189000283
Product Length/Depth	Product Height
4 in	2.13 in
Product Width	Product Weight
4 in	0.84 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4"

Capacity

30.3 cubic in

Depth

2-1/8"

Conduit/cable

Conduit (no clamps)

Construction

Welded

Side knockouts

(8) 1/2 in, (4) 1/2 in, (1) 3/4 in E

Bottom Knockouts

(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E

Material

Steel

Special features

Includes ground screw with pigtail lead

Resources

Catalogs

[Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP403PF](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)