Specifications



Eaton TP451

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", VMS, Conduit (no clamps), Welded, 2-1/8", Steel, (6) 1/2", (3) 1/2", (1) 3/4" E, 30.3 cubic inch capacity

General specifications	
PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP451
UPC	786189104516
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.96 lb

Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
BRACKET STYLE	VMS
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(6) 1/2 in, (3) 1/2 in, (1) 3/4 in E
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
CERTIFICATION REPORTS	4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP451 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.

Specifications



Eaton TP451

Eaton Crouse-Hinds series Square Outlet Box, (2) 1/2", (2) 1/2", (1) 3/4" E, 4", VMS, Conduit (no clamps), Welded, 2-1/8", Steel, (6) 1/2", (3) 1/2", (1) 3/4" E, 30.3 cubic inch capacity

General specifications	
PRODUCT NAME	Eaton Crouse-Hinds series square outlet box
CATALOG NUMBER	TP451
UPC	786189104516
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	2.13 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.96 lb

Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

BOX SIZE	4"
CAPACITY	30.3 cubic in
DEPTH	2-1/8"
CONDUIT/CABLE	Conduit (no clamps)
BRACKET STYLE	VMS
CONSTRUCTION	Welded
SIDE KNOCKOUTS	(6) 1/2 in, (3) 1/2 in, (1) 3/4 in E
BOTTOM KNOCKOUTS	(2) 1/2 in, (2) 1/2 in, (1) 3/4 in E
MATERIAL	Steel

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
CERTIFICATION REPORTS	4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP451 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2025 Eaton. All Rights Reserved.