

Specifications



Photo is representative

Eaton TP519

Eaton Crouse-Hinds series Square Surface Cover, 4", Raised surface, Steel, For one 30 amp twist-lock single receptacle 1-23/32" diameter, 5.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square surface cover
CATALOG NUMBER	TP519
UPC	786189105193
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.37 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

BOX SIZE	4"
-----------------	----

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	5.5 cubic in
CONFIGURATION	Raised surface
MATERIAL	Steel
TYPE	For one 30 amp twist-lock single receptacle 1-23/32" diameter

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
CERTIFICATION REPORTS	4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP519 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative

Eaton TP519

Eaton Crouse-Hinds series Square Surface Cover, 4", Raised surface, Steel, For one 30 amp twist-lock single receptacle 1-23/32" diameter, 5.5 cubic inch capacity

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series square surface cover
CATALOG NUMBER	TP519
UPC	786189105193
PRODUCT LENGTH/DEPTH	4 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.37 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous
----------------------------	------------------------

Product specifications

BOX SIZE	4"
-----------------	----

	Locations
STANDARDS TYPE	NEC/CEC

CAPACITY	5.5 cubic in
CONFIGURATION	Raised surface
MATERIAL	Steel
TYPE	For one 30 amp twist-lock single receptacle 1-23/32" diameter

Resources

CATALOGS	Crouse-Hinds series 4-Inch Steel Square Boxes and Covers catalog page
CERTIFICATION REPORTS	4-Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification 4-Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TP519 Steel Outlet Boxes for Electrical Systems

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

