

# Specifications



## Eaton TP558

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (4) 3/4", (4) 1", 42.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP558
<b>UPC</b>	786189105582
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	1.04 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4-11/16"
<b>CAPACITY</b>	42 cubic in
<b>DEPTH</b>	2-1/8"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)

<b>CONSTRUCTION</b>	Drawn
<b>SIDE KNOCKOUTS</b>	(4) 3/4 in, (4) 1 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel

## Resources

### 3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP558 3D drawing](#)

### CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP558](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton TP558

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (4) 3/4", (4) 1", 42.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square outlet box
<b>CATALOG NUMBER</b>	TP558
<b>UPC</b>	786189105582
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	2.13 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	1.04 lb



### Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### Product specifications

<b>BOX SIZE</b>	4-11/16"
<b>CAPACITY</b>	42 cubic in
<b>DEPTH</b>	2-1/8"
<b>CONDUIT/CABLE</b>	Conduit (no clamps)

<b>CONSTRUCTION</b>	Drawn
<b>SIDE KNOCKOUTS</b>	(4) 3/4 in, (4) 1 in
<b>BOTTOM KNOCKOUTS</b>	(3) 1/2 in, (2) 3/4 in
<b>MATERIAL</b>	Steel

## Resources

### 3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds TP558 3D drawing](#)

### CATALOGS

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

### CERTIFICATION REPORTS

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - TP558](#)

[Steel Outlet Boxes for Electrical Systems](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

