

Eaton TP563

Catalog Number: TP563

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (6) 1/2", (6) 1/2", (1) 3/4" C, 42.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP563
	UPC
	786189105636
Product Length/Depth	Product Height
4.69 in	2.13 in
Product Width	Product Weight
4.69 in	1.04 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

42 cubic in

Depth

2-1/8"

Conduit/cable

Conduit (no clamps)

Construction

Drawn

Side knockouts

(6) 1/2 in, (6) 1/2 in, (1) 3/4 in C

Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

Material

Steel

Resources

3D CAD drawing package

[Eaton Crouse-Hinds TP563 3D drawing](#)

Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings](#)

[Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP563](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton TP563

Catalog Number: TP563

Eaton Crouse-Hinds series Square Outlet Box, (3) 1/2", (2) 3/4", 4-11/16", Conduit (no clamps), Drawn, 2-1/8", Steel, (6) 1/2", (6) 1/2", (1) 3/4" C, 42.0 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series square outlet box	TP563
	UPC
	786189105636
Product Length/Depth	Product Height
4.69 in	2.13 in
Product Width	Product Weight
4.69 in	1.04 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Box size

4-11/16"

Capacity

42 cubic in

Depth

2-1/8"

Conduit/cable

Conduit (no clamps)

Construction

Drawn

Side knockouts

(6) 1/2 in, (6) 1/2 in, (1) 3/4 in C

Bottom Knockouts

(3) 1/2 in, (2) 3/4 in

Material

Steel

Resources

3D CAD drawing package

[Eaton Crouse-Hinds TP563 3D drawing](#)

Catalogs

[Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

Certification reports

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings](#)

[Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP563](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)