

# Specifications



Photo is representative

## Eaton TP571

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, Steel, 3/4" raised, with ears 2-3/4", 5.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square cover
<b>CATALOG NUMBER</b>	TP571
<b>UPC</b>	786189105711
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	0.75 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	0.4 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**BOX SIZE** 4-11/16"

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>CAPACITY</b>	5 cubic in
<b>COLOR</b>	Natural
<b>CONFIGURATION</b>	Raised surface
<b>MATERIAL</b>	Steel
<b>TYPE</b>	3/4" raised, with ears 2-3/4"

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds TP571 3D drawing](#)

**CATALOGS** [Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

**CERTIFICATION REPORTS** [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

**SPECIFICATIONS AND DATASHEETS** [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP571](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.



# Specifications



Photo is representative

## Eaton TP571

Eaton Crouse-Hinds series Square Cover, 4-11/16", Natural, Raised surface, Steel, 3/4" raised, with ears 2-3/4", 5.0 cubic inch capacity

### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series square cover
<b>CATALOG NUMBER</b>	TP571
<b>UPC</b>	786189105711
<b>PRODUCT LENGTH/DEPTH</b>	4.69 in
<b>PRODUCT HEIGHT</b>	0.75 in
<b>PRODUCT WIDTH</b>	4.69 in
<b>PRODUCT WEIGHT</b>	0.4 lb



### Certifications and compliances

**AREA CLASSIFICATION** Ordinary/Non-Hazardous

### Product specifications

**BOX SIZE** 4-11/16"

	Locations
<b>STANDARDS TYPE</b>	NEC/CEC

<b>CAPACITY</b>	5 cubic in
<b>COLOR</b>	Natural
<b>CONFIGURATION</b>	Raised surface
<b>MATERIAL</b>	Steel
<b>TYPE</b>	3/4" raised, with ears 2-3/4"

## Resources

**3D CAD DRAWING PACKAGE** [Eaton Crouse-Hinds TP571 3D drawing](#)

**CATALOGS** [Crouse-Hinds series 4-11/16 Inch Steel Square Boxes and Covers catalog page](#)

**CERTIFICATION REPORTS** [4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings Canadian certification](#)

[4-11/16 Inch Steel Square Outlet Boxes, Covers, Extension Rings UL certification](#)

**SPECIFICATIONS AND DATASHEETS** [Steel Outlet Boxes for Electrical Systems](#)

[Eaton Specification Sheet - TP571](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

---

Reserved.

